Inweld 320-16

AWS A5.4 E320-16

Chemical Composition of Inweld 320-16

					Cb (Nb)						
Fe	С	Cr	Ni	Мо	& Ta	Mn	Si	Р	S	Ν	Cu
Balance	0.07	19.0	32.0	2.0-3.0	8 X C	0.5-2.5	0.60	0.04	0.03		3.0-4.0
		-21.0	-36.0		- 1.00						

Single values are maximum unless otherwise specified.

Description and Applications

Inweld 320-16 coated electrodes are used for welding Carpenter 20 or 20 Cb-3 stainless steel. Often referred to as 320Cb-16 or 20 Cb-3*, this electrode produces weld deposits that resist chemical corrosion from sulfuric acid, phosphoric acid and their salts. Inweld 320-16 is used to weld both castings and wrought alloys of similar analysis without having to do post-weld heat treatment. The Columbium (Cb) content of this electrode gives 320-16 weld deposits excellent resistance to inter-granular corrosion.

Procedure

Clean the work area. Preheating is not required. Use DC+ (reverse polarity), however an AC machine with a minimum open circuit voltage of 70 volts can be used. The welding current should be kept to a minimum and the welding speed at a maximum to avoid overheating and distortion. The arc length should be kept as short as possible without touching the flux-coating of the electrode to the molten weld pool. The electrode should be tilted 15° in the direction of travel. Stringer beads should be used in the flat, horizontal, & overhead positions. Vertical welding should be done using the weaving technique but not to exceed 2-3 times the diameter of the electrode. Be sure to remove all slag before making additional passes. On the final pass, allow the part to cool before removing the slag cover.

Typical Weld Metal Properties

	AWS Spec
Tensile Strength:	<mark>85,0</mark> 00 psi
Yield Strength:	57,000 psi
Elongation:	34%
Recommende	ed Parameters

SMAW AC/DC+ (Electrode Positive)

Wire Diameter	Flat Amperage	Vertical & Overhead Amperage
3/32"	70-85	65-75
1/8"	85-110	80-90
5/32"	110-140	100-120
3/16"	120-160	110-130

INWELDCORPORATION.COM

Pennsylvania 3962 Portland Street Coplay, PA 18037 North Carolina 1029 S. Marietta St. Gastonia, NC 28054 Texas 9300 Lawndale St. Houston, TX 77012 California 6201 Coliseum Way, Unit A Oakland, CA 94621